

FICHE  
TECHNIQUE  
DATA SHEET

Refrigerated glass catafalque  
Reference: MC001018

[www.hygeco.com](http://www.hygeco.com)





## Refrigerated glass catafalque



Reference: MC001018



## 1. Product description

The refrigerated catafalque is designed for the temporary display of a coffin in a funeral centre. It has a stainless-steel frame with a light oak textured Formica side panel. Its large glass surface gives perfect visibility of the coffin.



There are a stainless-steel roller and a mobile trolley inside the catafalque. They make it easy to insert the coffin. A side door with key lock opens easily to 180°. The interior dimensions of the catafalque accommodate most coffins on the market.

The catafalque is equipped with a refrigeration system to ensure uniform temperature throughout.

## 2. Technical data

Length:	2480 mm
Width:	900 mm
Height:	1425 mm
Net weight:	About 550 kg
Payload:	200 kg
Finish:	Stainless steel frame / Oak textured Formica
Wheels:	Four wheels Ø 100 mm
Power supply:	230V / 50 / 16A
Door opening:	Side opening to 180 ° with a key lock
Interior temperature:	4°- 6°C
Power Watt:	996 Watt
Refrigerant:	R452A



---

### 3. Installation and use

The catafalque must be installed and operated on level ground.

---

### 4. Related product



**FP000158 with FP000154:** Height adjustable coffin trolley with rollers is designed for transporting coffins in the funeral industry. It features a sturdy frame as well as a roller option with a locking system ensuring excellent coffin securing. The trolley is made entirely of stainless steel. Its reliable oleo-dynamic jack, operated by a foot pedal, positions the coffin at the desired height in complete safety for loading or unloading into a glass catafalque. The Ø200 mm wheels make handling easy and silent.




---

### 5. Packaging

A wooden box L/I/H: **2700 x 1050 x 1500 mm** – Gross weight: **750 kg**

The catafalque is delivered in a wooden box designed to protect it during transport. Transport does not require any special precautions, but care must be taken to avoid bumping or tipping. The wooden box is not stackable.

Make sure there are enough qualified people to handle the box. Please transport it using a pallet truck or motorised forklift. Manoeuvre carefully to avoid damaging the equipment. Always transport the pallet in its original packaging; do not remove the packaging before transport.





## 6. CE Certificates / Norms / ISO

Hygeco International products holds the ISO 9001: 2015 certification registered under No. FR084950-1 valid until December 18, 2026.

We certify that our products are conditioned, packaged and labelled in compliance with standards in accordance with our internal charter and considering the specific requirements of our customers.



## 7. Drawing

